

CILP - 10 PORTABLE INDUCTION LOOP SYSTEM

Designed as a highly portable free standing system to provide communication for people wearing a hearing aid and the 'T' facility. Suitable for use in a wide range of applications in meetings rooms, customer service counters, receptions and interview areas.



- Portable and easy to carry
- Very quick and simple to set up
- Integral microphone
- External microphone socket
- Microprocessor controlled latest technology for optimum reception of speech and to conserve battery life
- Powered by rechargeable batteries with more than 24 hours use from full charge
- LED indications of speech and battery status
- Plug in Power Adaptor for recharging and continuous use
- Elegant and robust ABS plastic construction

CILP - 10
PORTABLE
INDUCTION
LOOP SYSTEM

CLOCKAUDIO


SPECIFICATIONS

Portable Induction Loop

HEIGHT	250mm (9.8 ins.)
WIDTH	275mm (10.8 ins.)
DEPTH	110mm (4.3 ins.)
WEIGHT	500gms (17.6 oz.)
POWER	Rechargeable 12v internal battery
BATTERY LIFE	≥24 Hours
MICROPHONE	Condenser (back electret)
POLAR PATTERN	Omni Directional
EXTERNAL MICROPHONE CONNECTOR	2.5mm jack plug socket
POWER ADAPTOR CONNECTION (12V)	2.1mm jack plug socket

OPTIONAL EXTRAS

Suggested external microphone
Clockaudio C006 Boundary Layer
CL5 Lavalier



CLOCKAUDIO®

Clockaudio Ltd - Headquarters

22 Arside Road, Waterlooville, Hampshire PO7 7UR, UK
Tel +44 (0)23 9225 1193 • Fax +44 (0)23 9225 1201
e-mail sales@clockaudio.co.uk

Clockaudio North America Inc.

2891 du Meunier; Unit 103, Vaudreuil-Dorion, Quebec J7V 8P2, Canada
Tel: (450) 424-9797 • Fax: (450) 424-3660
e-mail: info@clockaudio.com

www.clockaudio.com

PROFESSIONAL
MICROPHONE
SYSTEMS

As part of a continuous product improvement programme, we reserve the right to alter specifications without prior notice.